

Solid wire & Stranded wire : Recommended wire and Stripping length


■ Solid wire, Stranded wire (Except using ferrule terminals)

Recommended wire		Stripping length (mm)
(mm ²)	(AWG)	
0.2-4	24-12	9-11

Ferrule terminal processing wire

■ Using ferrule terminals

Recommended wire		Ferrule conductor length (mm)
(mm ²)	(AWG)	
0.5	20	10 or 12
0.75	18	
1	18	
1.5	16	
2.5	14	



NOTES

A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

B : M3 EMBOSSED, TAPPED AND COUNTERSUNK HOLES (4) FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6mm.

(unit : mm)

MODEL NAME	HWS100A/EHA
TDK-Lambda	
A287-02-01/EHA	