


**NOTES**

- A : MODEL NAME, OPTION CODE, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B : M3 EMBOSSED, TAPPED AND COUNTERSUNK HOLES (4) FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6mm.
- C: REMOTE ON/OFF CONTROL CONNECTOR --- OPTION B2B-XH-AM (JST)  
 MATCHING HOUSING : XHP-2 (JST)  
 MATCHING TERMINAL PIN : BXH-001T-P0.6 (JST) OR SXH-001T-P0.6 (JST)  
 HAND CRIMPING TOOL : YC-110R (JST) OR YRS-110 (JST)  
 MATCHING HOUSING AND TERMINAL PIN --- NOT INCLUDED WITH THE PRODUCT



**ACCESSORIES**

\* SHORT PIECE (NET 2) FOR SHORTING PURPOSE (+S~+V, -S~-V) : MOUNTED AT TIME OF SHIPMENT.

**OPTIONAL MODELS**

| MODEL            | REMOTE ON/OFF CONTROL |
|------------------|-----------------------|
| HWS150A-*        | -                     |
| HWS150A-* [ /R ] | ○                     |

(unit : mm)

|                   |         |
|-------------------|---------|
| MODEL NAME        | HWS150A |
| <b>TDK-Lambda</b> |         |
| A259-02-01B       |         |