






== FRONT SIDE SCREW ==



== NOTES ==

A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

B : 9-M4 BR & COUNTERSINK ARE FOR CUSTOMER'S CHASSIS MOUNTING. (SCREW PENETRATION DEPTH 6mm MAX.)



D : GENERAL TOLERANCE : ±0.5

== ACCESSORIES ==

- * TERMINAL COVER 1 ----- (NET 1)
(ATTACHED ON TERMINAL AT SHIPMENT)
- * TERMINAL COVER 2 ----- (NET 1)
(ATTACHED ON TERMINAL AT SHIPMENT)
- * SHORT PIECE 1 ----- (NET 1)
SHORTING -R—AG
(ATTACHED ON CN41 AT SHIPMENT)
- * SHORT PIECE 2 ----- (NET 1)
SHORTING +L—+S, -L—-S
(ATTACHED ON CN61 AT SHIPMENT)

| | | | | |
|-------|----------------------|-------------|------------|--|
| SCALE | 1 / 2 | TITLE | HWS3000GT4 | |
| UNITS | mm | DRAWING No. | A294-02-01 | |
| ANGLE | 3RD ANGLE PROJECTION | PAGE | E1 / 1 | |

TDK-Lambda