


SIGNAL CONNECTOR INFORMATION



== ACCESSORIES ==


- * COVER FOR BARRIER TERMINAL STRIP -----1 (ATTACHED ON TERMINAL AT SHIPMENT)
- * SHORT PIECE -----1 SHORTING +Vm --- +S, -Vm --- -S, CNT --- TOG (ATTACHED ON CN1 AT SHIPMENT)

== SIGNAL CONNECTOR USED ==

| PART DESCRIPTION | PART NAME | MANUFACT |
|------------------|------------|----------|
| PIN HEADER | S12B-PHDSS | JST |

== MATCHING HOUSINGS , PINS & TOOL ==

| PART DESCRIPTION | PART NAME | MANUFACT |
|--------------------|------------------------------------------------------|----------|
| SOCKET HOUSING | PHDR-12VS | JST |
| TERMINAL PINS | SPHD-002T-P0.5(AWG28~24) SPHD-001T-P0.5(AWG26~22) | JST |
| HAND CRIMPING TOOL | YRS-620(SPHD-002T-P0.5) YC-610R(SPHD-001T-P0.5) | JST |



== NOTES ==

- A: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B : M4 TAPPED HOLES (8) FOR CUSTOMER CHASSIS MOUNTING. (SCREW PENETRATION DEPTH 6m/m MAX.)

(unit : mm)

| | |
|-------------------|-----------|
| MODEL NAME | HWS300/PV |
| TDK-Lambda | |
| A231-02-01/PV-C | |