


NOTES

- A: MODEL NAME, OPTION, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT AND COUNTRY OF MANUFACTURE ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B: M4 EMBOSSED, TAPPED AND COUNTERSUNK HOLES (7) FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6m/m.
- C: $\phi 4.5$ HOLES (2) FOR CUSTOMER CHASSIS MOUNTING. (USE M4 MOUNTING SCREWS.)
- D: REMOTE ON/OFF CONTROL CONNECTOR --- OPTION B2B-XH-A (JST)

ACCESSORIES

- * COVER FOR BARRIER STRIP TERMINAL.
 - * SHORT PIECE (NET 2) FOR SHORTING PURPOSE (+S~+V, -S~-V):MOUNTED AT TIME OF SHIPMENT.
 - * HOUSING: XHP-2 (JST), TERMINAL: BXH-001T-P0.6 (JST) OR SXH-001T-P0.6 (JST) --- OPTION
- HAND CRIMPING TOOL : YC-110R (JST) OR YRS-110 (JST)



OPTIONAL MODELS

MODEL	COVER	REMOTE ON/OFF CONTROL
JWS150-*		
JWS150-*/A	○	
JWS150-*/R		○
JWS150-*/RA	○	○

(unit : mm)

MODEL NAME	JWS150
TDK-Lambda	
A160-02-01E	