



\*TERMINAL ASSIGNMENTS

①.....AC(N) } INPUT

②.....AC(L) }

③.....-V } OUTPUT

④.....+V }

\*MATERIAL

CASE : PLASTIC(UL94V-0)

PBT t=1.0mm

NOTES

A: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE, MARKING AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

B: INPUT AND OUTPUT TERMINALS : 4-φ1±0.1

C: UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE : ±0.3

(unit : mm)

MODEL NAME	KWS15A
<b>TDK-Lambda</b>	
FC004-02-01A	