




SEE NOTE A



SEE NOTE A



SEE NOTE B

A. MODEL NAME NOMINAL OUTPUT VOLTAGE AND MAXIMUM OUTPUT CURRENT ARE SHOWN IN THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATION.

B. M3 TAPPED & EMBOSSED & COUNTERSUNK HOLES (7) FOR CUSTOMER CHASSIS MOUNTING. SCREW MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 5mm.

C. SWITCH IS SELECTED TO 230V BEFORE SHIPMENT.

(unit : mm)	
MODEL	LS150
TDK-Lambda	
PA579-02-01E	