


SIGNAL CONNECTOR INFORMATION



SIGNAL CONNECTOR USED

PART DESCRIPTION	PART NAME	MANUFACT
PIN HEADER	S8B-PHDSS(LF)(SN) (CN2)	JST



MATCHING HOUSINGS, PIN & TOOL

PART DESCRIPTION	PART NAME	MANUFACT
SOCKET HOUSING	PHDR-8VS (CN2)	JST
TERMINAL PINS	SPHD-002T-P05(AWG#28-24) SPHD-001T-P05(AWG#28-22)	JST
HAND CRIMPING TOOL	YRS-620(SPHD-002T-P0.5) YC-610R(SPHD-001T-P0.5)	JST

ACCESSORIES

SHORT PIECE -----  
 SHORTING +V, -+S, -V, -S, CNT+, -CNT-  
 (ATTACHED ON CN2 AT SHIPMENT)

NAME PLATE



NOTES

- A. MODEL NAME NOMINAL OUTPUT VOLTAGE AND MAXIMUM OUTPUT CURRENT ARE SHOWN IN THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATION.
- B. M4 COUNTERSUNK & EMBOSSED HOLES (2) FOR CUSTOMER CHASSIS MOUNTING SCREW MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 5mm.
- C. M4 COUNTERSUNK & EMBOSSED HOLES (9) FOR CUSTOMER CHASSIS MOUNTING SCREW MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6mm.