



Notes

A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (For only approved products) are shown here in accordance with the specifications.

B: M3 tapped holes 4 for customer chassis mounting (FG). Screws must not protrude into power module by more than 12.7mm. (Back side for heat sink.)

C: Input and output terminal... ( 5- $\phi$ 2  
5- $\phi$ 0.6

(unit : mm)

MODEL NAME	PF500A-360
<b>TDK-Lambda</b>	

C108-02-011