



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, SEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Output terminal : 6-φ2
- D: Input and Intermediate terminal : 5-φ2
- E: Signal pin (+S, -S, TRIM, ENA, IOG, AUX, +ON/OFF, -ON/OFF, PC, COM) : 10-□0.64
- F: Unless otherwise specified dimensional tolerance : ±0.3

(unit : mm)

MODEL NAME	PFE1000F
DENSEI-LAMBDA	
C251-02-01B	