

CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B2P3-VH	J.S.T.	1
PIN HEADER (OUTPUT SIDE CN51)	B4P-VH	J.S.T.	1

MATCHING HOUSINGS, PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING (CN1)	VAR-2/VHR-3N	J.S.T.	1
SOCKET HOUSING (CN51)	VHR-4N	J.S.T.	1
TERMINAL PINS	SVH-21T-P1.1	J.S.T.	6
	BVH-21T-P1.1		
HAND CRIMPING TOOL	YC-930R	J.S.T.	-
	YC-931R		
HOUSING(CN2)	22~18AWG: STO-21T-250N	J.S.T.	1
	18~14AWG: STO-61T-250N		

NOTES

A: M3 EMBOSSED TAPPED & COUNTERSINK HOLES (4) ARE FOR CUSTOMER'S CHASSIS MOUNTING.

B: ø3.5 HOLES (2) AND R1.75 SLOT HOLES (2) ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLES.

C: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

D: CN2 IS FOR SAFETY GROUND (FG) CONNECTION IN CLASS I.

(unit : mm)

MODEL NAME	ZWS50C/L
TDK-Lambda	

FA014-02-01/L-A