

**Standard Reliability Prediction Report**

**Part Number** DSP 60-5  
**Model** Bellcore Lssue 6  
**Method** Method Case 3  
**Environment** GB, GC - Ground Benign, Controlled  
**Temperature** 40.00

**Description** Top-level assembly  
**Input Voltage** SRA4M-05.RPJ  
**Date** Feb 21, 2006  
**Failure Rate** 1.679525  
**MTBF** 595,406

Assembly Name	Part Number	Ref Des	Qty	Failure Rate	MTBF
DSP 60-5			1.00	1.679525	595,406
Connection			1.00	0.071484	13,989,183
Transistor			1.00	0.134401	7,440,445
Fuse			1.00	0.009000	111,111,111
PCB			1.00	0.011400	87,719,298
Diode			1.00	0.133237	7,505,437
Capacitor			1.00	0.693408	1,442,152
Zeners			1.00	0.053538	18,678,374
Resistors			1.00	0.074052	13,503,938
ICs			1.00	0.353991	2,824,929
Opto-couplers			1.00	0.108000	9,259,259
Core			1.00	0.001464	683,247,906
Transformers			1.00	0.035551	28,128,796