

Certificate



Certificate no.

TA 50608190 01

License Holder:

TDK-Lambda Americas Inc.
401 Mile of Cars Way, Suite 325,
National City, CA 91950
USA

Manufacturing Plant:

040-0001729524

Test report no.: ZTW1-RC 10043565 007

Client Reference: P01255431

Tested to:

IEC 60601-1:2005+A1
EN 60601-1:2006+A1+A12
IEC 60601-1-6:2010+A1
EN 60601-1-6:2010+A1
IEC 62366:2007+A1
EN 62366:2008+A1

Certified Product: (AC Power Adapter)

License Fee - Units

Type Designation : DTM65PWXXXC8-ZZZ (TDK-Lambda)
XXX stands for : 050, 120, 150, 190, 240, 280, 480
Z stands for : A-Z, 0-9 or blank
Rated Voltage : AC 100-240V, 50-60Hz
Rated Current : 2-1A
Output Voltage : see Appendix
Output Current : see Appendix
max. Ambient Temperature: 40°C
Protection Class : II

Remark : This certificate is valid for maximum 5 years.

Licensed Test mark:



Regular
Production
Surveillance

www.tuv.com
ID 1111277112

TÜV Rheinland Taiwan Ltd

Signature

Dipl.-Ing. (FH) A. Klinker



Date of Issue

(day/mo/yr)

21/11/2023

Appendix to TÜV approved Certificate No.: TA 50608190

Certified Product : AC Power Adapter
Report Number : 10043565 007
Type Designation : DTM65PWXXXC8-ZZZ
 (XXX = 050, 120, 150, 190, 240, 280, 480; Z = A-Z, 0-9 or blank)

Model TDK-Lambda	Rating		
	Output Voltage	Output Current	Max. Output Power
DTM65PW050C8-ZZZ	5	8	40
DTM65PW120C8-ZZZ	12	5	60
DTM65PW150C8-ZZZ	15	4	60
DTM65PW190C8-ZZZ	19	3.42	65
DTM65PW240C8-ZZZ	24	2.7	65
DTM65PW280C8-ZZZ	28	2.32	65
DTM65PW480C8-ZZZ	48	1.35	65

Date: 21st November, 2023

Certification Body



Dipl.-Ing. (FH) A. Klinker