

Certificate



Certificate no.

TA 50398173 03

License Holder:

TDK-Lambda Americas Inc.
401 Mile of Cars Way, Suite 325,
National City, CA 91950
USA

Manufacturing Plant:

040-0001729524

Test report no.: ZTW1-RC 50070018 007

Client Reference: P01354196

Tested to:

IEC 60601-1:2005+A1+A2
EN 60601-1:2006+A1+A12+A2
IEC 60601-1-6:2010+A1+A2
EN 60601-1-6:2010+A1+A2
IEC 62366-1:2015+A1
EN 62366-1:2015+A1

Certified Product: AC POWER ADAPTER

License Fee - Units

as page 01

Change

Test Requirement : see above

Change for Type Designation: DTM65PWXXXD-ZZZ

Type Designation : DTM65PWXXXDZZZZ (TDK-Lambda)

XXX stands for : 050, 120, 150, 190, 240, 280,
360 or 480

Z stands for : blank, 0 to 9, "-" or A to Z

Outputs : see Appendix

Remark: This certificate is valid for maximum 5 years from
last page.

Licensed Test mark:



IEC 60601-1
EN 60601-1

www.tuv.com
ID 1419054642

TÜV Rheinland Taiwan Ltd

Signature

Dipl.-Ing. (FH) A. Klinker

Date of Issue

(day/mo/yr)

08/03/2024



Appendix to TÜV approved Certificate No.: TA 50398173

Certified Product : Medical Power Supply
Report Number : 50070018 007
Type Designation : DTM65PWXXXDZZZZ
 (XXX can be 050, 120, 150, 190, 240, 280, 360 or 480, Z can be blank, 0 to 9, "-" or A to Z)

Model name	Output rating		
	Output Voltage [Vdc]	Output Current [A]	Output Power [W]
DTM65PW050DZZZZ	+5	8.0	40
DTM65PW120DZZZZ	+12	5.0	60
DTM65PW150DZZZZ	+15	4.0	60
DTM65PW190DZZZZ	+19	3.42	65
DTM65PW240DZZZZ	+24	2.71	65
DTM65PW280DZZZZ	+28	2.32	65
DTM65PW360DZZZZ	+36	1.81	65
DTM65PW480DZZZZ	+48	1.35	65

Date: 8^h March, 2024

Certification Body



Dipl.-Ing. (FH) A. Klinker