

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Name and address of the factory	DONGGUAN CINCON ELECTRONICS LTD 1 JING XIANG RD DONGCHENG FOREIGN TRADE INDUSTRIAL PARK ZHUSHAN DONGCHENG DISTRICT DONGGUAN, GUANGDONG, 523128 CHINA
Note: <i>When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	Additional Information on page 2 Input: 100-240V ac, 50-60 , 0.5 A, AC Output: 5W, DC , Marked ; Insulation Class: Class II Additional Information on page 2
Trademark (if any)	 TDK-Lambda
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	KPSA 15, KPSA10, KPSA5 Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A6048-CB-1 issued on 2021-02-11

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-02-11

Signature:
Jan-Erik Storgaard

Factories:

CINCON ELECTRONICS CO LTD
8-1 FU KUNG RD
FU HSING PARK
FU HSING HSIANG CHANGHUA HSIEN 506
TAIWAN

Additional Model(s):

Series: KPSA10, KPSA10-xx

where XX is output voltage expressed in volts, capital letter 'R' used in lieu of decimal place,
example: KPSA10-3R3 has output power 10W and voltage 3.3 Vdc.

KPSA 15, KPSA15-xx

where XX is output voltage expressed in volts, capital letter 'R' used in lieu of decimal place,
example: KPSA15-3R3 has output power 15W and voltage 3.3 Vdc.

KPSA5, KPSA5-xx

where XX is output voltage expressed in volts, capital letter 'R' used in lieu of decimal place,
example: KPSA5-3R3 has output power 5W and voltage 3.3 Vdc.

Model Name: KPSA 15: Input: 100-240V ac; 50-60 ; 0.5 A; AC
Output: 5W, DC , Marked ; Insulation Class: Class II

Model Name: KPSA10: Input: 100-240V ac; 50-60 ; 0.5 A; AC
Output: 10W, DC , Marked ; Insulation Class: Class II

Model Name: KPSA5: Input: 100-240V ac; 50-60 ; 0.25 ; AC
Output: 5W, DC , Marked ; Insulation Class: Class II

Additionally evaluated to:

EN 62368-1:2014/AMD11:2017, EN 62368-1:2014

Additional information (if necessary)

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-02-11

Signature:

Jan-Erik Storgaard