

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product

Switch Mode Power supply

Name and address of the applicant

TDK-LAMBDA UK LTD  
KINGSLEY AVE  
ILFRACOMBE, EX34 8ES United Kingdom

Name and address of the manufacturer

TDK-LAMBDA UK LTD  
KINGSLEY AVE  
ILFRACOMBE, EX34 8ES United Kingdom

Name and address of the factory

Note: When more than one factory, please report on page 2

CINCON ELECTRONICS CO LTD  
8-1 FU KUNG RD  
FU HSING PARK  
FU HSING HSIANG  
CHANGHUA HSIEN, 506 Taiwan Additional Information on page 2

Ratings and principal characteristics

ZPSA20: 100-240V, 0.5A, 50-60Hz  
ZPSA40: 100-240V, 1.2A, 50-60Hz  
ZPSA60: 100-240V, 1.4A, 50-60Hz

Trademark / Brand (if any)

TDK-Lambda



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

ZPSAx-yz  
See Page 2

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E135494-A6046-CB-2 issued on 2020-11-19

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-11-20

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

**DK-106023-UL**

**Model Details:**

ZPSAx-yz Where x may be replaced with 20, 40 or 60 and y may be replaced with any number between 3R3-24 (ZPSA20), or 3R3-48 (ZPSA40 & ZPSA60) and z may be "/SE" or blank

**Factories:**

DONGGUAN CINCON ELECTRONICS LTD  
1 JING XIANG RD DONGCHENG  
FOREIGN TRADE INDUSTRIAL PARK  
ZHUSHAN DONGCHENG DISTRICT  
DONGGUAN, 523128 GUANGDONG China

**Additional Information:**

Additionally evaluated to EN 62368-1:2014 / A11: 2017; National Differences specified in the CB Test Report.

**Additional information (if necessary)**



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-11-20

Signature:

Jan-Erik Storgaard