



Ref. Certif. No.

JP-26072-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Name and address of the manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Name and address of the factory	TDK-LAMBDA (CHINA) ELECTRONICS CO LTD NO.95, ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028 CHINA
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	ZWS30B-abcdefg a = 3, 5, 12, 15, 24 or 36. b = "/" or blank. c = "A", "L" or blank. d = "CO2" or blank. e = "FG" or blank. f = "FV" or blank. g = "N" or blank
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014/ A11:2017. National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E122103-A6243-CB-1 issued on 2022-04-13 E122103-A6243-CB-1 issued on 2022-04-12

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-04-14

Signature: Masamichi Takagi



Ref. Certif. No.

JP-26072-UL

Factory(ies):

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
NO.15 TONGXIN RD, ZHAOFENG ECONOMIC DEVELOPMENT ZONE, LEYU TOWN ZHANGJIAGANG JIANGSU 215622
CHINA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR
MALAYSIA

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

Ratings:

Input: AC100-240V, 50-60Hz or 50/60Hz,
0.5A (for model ZWS30B-3bcdefg),
0.65A (except for models ZWS30B-3bcdefg and ZWS30B-36bcdefg)
1.0A (for model ZWS30B-36bcdefg)

Output :

ZWS30B-3bcdefg:
2.97-3.63Vdc, Maximum 6A, Maximum 19.8W

ZWS30B-5bcdefg:
4.5-5.5Vdc, Maximum 6A, Maximum 30.0W

ZWS30B-12bcdefg:
10.8-13.2Vdc, Maximum 2.5A; Maximum 30.0W

ZWS30B-15bcdefg:
13.5-16.5Vdc, Maximum 2.0A; Maximum 30.0W

ZWS30B-24bcdefg:
21.6-26.4Vdc, Maximum 1.3A; Maximum 31.2W

ZWS30B-36bcdefg:
32.4-39.6Vdc, Maximum 0.9A; Maximum 32.4W


Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2022-04-14

Signature: 
Masamichi Takagi