

ZPSA20 SERIES			ZPSA40 SERIES			ZPSA60 SERIES		
Model	No Load Powe		Model	No Load Powe		Model	No Load Powe	
Voltage	115V	230V	Voltage	115V	230V	Voltage	115V	230V
ZPSA20-3R3	0.27W	0.36W	ZPSA40-3R3	0.28W	0.5W	ZPSA60-3R3	0.28W	0.46W
ZPSA20-5	0.25W	0.34W	ZPSA40-5	0.38W	0.68W	ZPSA60-5	0.33W	0.5W
ZPSA20-9	0.25W	0.34W	ZPSA40-9	0.29W	0.48W	ZPSA60-9	0.2W	0.43W
ZPSA20-12	0.26W	0.35W	ZPSA40-12	0.33W	0.52W	ZPSA60-12	0.31W	0.51W
ZPSA20-15	0.33W	0.42W	ZPSA40-15	0.4W	0.6W	ZPSA60-15	0.34W	0.53W
ZPSA20-24	0.37W	0.46W	ZPSA40-24	0.43W	0.63W	ZPSA60-24	0.38W	0.59W
			ZPSA40-28	0.49W	0.69W	ZPSA60-28	0.48W	0.63W
			ZPSA40-30	0.57W	0.8W	ZPSA60-30	0.51W	0.67W
			ZPSA40-36	0.55W	0.75W	ZPSA60-36	0.37W	0.53W
			ZPSA40-48	0.62W	0.85W	ZPSA60-48	0.68W	0.85W