



FRONT DISPLAY DETAILS



SIGNAL CONNECTOR INFORMATION



== SIGNAL CONNECTOR USED ==

PART DESCRIPTION	PART NAME	MANUFACT
PIN HEADER	S16B-PADSS-1(LF)(SN)	JST

== MATCHING HOUSINGS, PINS & TOOL ==

PART DESCRIPTION	PART NAME	MANUFACT
SOCKET HOUSING	PADP-16V-1-S	JST
TERMINAL PINS	SPH-001T-P0.5L(AWG26~22) SPH-002T-P0.5L(AWG28~24)	JST
HAND CRIMPING TOOL	AP-K2N	JST

== RS 485 CONNECTOR USED ==

PART DESCRIPTION	PART NAME	MANUFACT
PIN HEADER	TM21R-5C-88(50)	HIROSE

== NOTES ==

A : MODEL NAME, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN IN THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS.

B : M4 TAPPED HOLES (BOTTOM net.8) FOR CUSTOMER CHASSIS MOUNTING. (SCREW PENETRATION DEPTH 6mm MAX.)

C : UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE : ±0.5

(unit : mm)

MODEL NAME	EZA2500W-32048
------------	----------------

TDK-Lambda

V010-02-01B