



NOTES :

A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (for only approved products) are shown here in accordance with the specifications.

B: Input, Output and signal terminals : $6-\phi 1.0\pm 0.1$

C: Unless otherwise specified dimensional tolerance : ± 0.5

(unit : mm)

MODEL NAME	CCG15-24-xxD
TDK-Lambda	

C282-02-01B