



NOTES :

A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (for only approved products) are shown here in accordance with the specifications.

B: Input, Output and signal terminals :  $6-\phi 1.0 \pm 0.1$

C: Unless otherwise specified dimensional tolerance :  $\pm 0.5$

(unit : mm)

MODEL NAME	CCG30-24-xxS
<b>TDK-Lambda</b>	

C266-02-01C