



Notes :

- A: Model name, Input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (For only approved products) are shown here in accordance with the specifications.
- B:  $\phi 4.5$  holes 2 for customer chassis mounting.
- C: M4 Embossed, tapped BR and countersunk holes 2 for customer chassis mounting. Screws must not protrude into power supply by more than 6mm.
- D: Unless otherwise specified dimensional tolerance :  $\pm 0.3$

CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACTURER
PIN HEADER REMOTE (CN2)	B2B-XH	JST

SCALE	1/1	TITLE	CCGS30-24-xxD
			OUTLINE
UNITS	mm	DRAWING No.	C321-02-01 <span style="border: 1px solid black; padding: 2px;">A</span> <span style="border: 1px solid black; padding: 2px;">PAGE 1/2</span>
ANGLE	3RD ANGLE PROJECTION	<b>TDK-Lambda</b>	