




CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACTURER
PIN HEADER REMOTE (CN2)	B2B-XH	JST

- Notes :
- A: Model name, Input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (For only approved products) are shown here in accordance with the specifications.
 - B: Ø4.5 holes 2 for customer chassis mounting.
 - C: M4 Embossed, tapped BR and countersunk holes 2 for customer chassis mounting. Screws must not protrude into power supply by more than 6mm.
 - D: Unless otherwise specified dimensional tolerance : ±0.3

SCALE	1 / 1	TITLE	CCGS30-24-xxS	
			OUTLINE	
UNITS	mm	DRAWING No.	C319-02-01	PAGE 1 / 2
ANGLE	3RD ANGLE PROJECTION	TDK-Lambda		