



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture are shown here in accordance with the specifications.
- B: M3 threaded holes 4 for customer chassis mounting (FG).
- C: Output terminals : 2-ø2
- D: Input and signal terminals : 8-ø1
- E: Unless otherwise specified dimensional tolerance : ±0.25

(unit : mm)

MODEL NAME	CN200B110/CO
TDK-Lambda	

CA938-02-01/CO