



NOTES :

A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (For only approved products) are shown here in accordance with the specifications.

B: M3 tapped holes 4 for customer chassis mounting (FG).

C: Input and output terminal : 8- ϕ 2

D: Signal pin : 8- ϕ 1

E: Unless otherwise specified dimensional tolerance : ± 0.3

(unit : mm)

MODEL NAME	PAF500F24-*
TDK-Lambda	

C169-02-01F