





NAME PLATE :



NOTE :

1. MODEL NAME, INPUT VOLTAGE RANGE, MAXIMUM INPUT CURRENT, NOMINAL OUTPUT VOLTAGE AND MAXIMUM OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
2. COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
3. M3 TAPPED HOLES (4) FOR CUSTOMER CHASSIS MOUNTING.
4. INPUT AND OUTPUT TERMINAL : 10-φ1.0
5. UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE : ±0.25

(unit : mm)

MODEL NAME	PAH75D24
TDK-Lambda	

PA565-02-01C