



NOTES :

A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (for only approved products) are shown here in accordance with the specifications.

B: $\varnothing 3.3$ holes 4 for customer chassis mounting (FG).

C: Input and Output pin : 8- $\varnothing 2$

D: Signal pin : 8- $\varnothing 1$

E: Unless otherwise specified dimensional tolerance : ± 0.3 mm

(unit : mm)

MODEL NAME	PH1200A280/T
TDK-Lambda	

CA888-02-01/T-A