



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (for only approved products) are shown here in accordance with the specifications.
- B: $\phi 3.3$ holes 4 for customer chassis mounting (FG).
- C: Output terminals : 4- $\phi 2$
- D: Input and signal terminals : 6- $\phi 1$
- E: Unless otherwise specified dimensional tolerance : ± 0.25

(unit : mm)

MODEL NAME	PH300A280/T
TDK-Lambda	

CA836-02-01/T-E