



Notes

A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (UL, C-UL [LEVEL5], SEMKO & CE marking) are shown here in accordance with the specifications.

B: M3 tapped holes 4 for customer chassis mounting (FG). Screws must not protrude into power module by more than 12.7mm. (Back side for heat sink.)

C: Input and output terminal... (10- $\phi 2$, 8- $\phi 0.6$)

(unit : mm)

MODEL NAME	PH300F280-*
TDK-Lambda	
C077-02-01H	