



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (for only approved products) are shown on the name plate in accordance with the specifications.
- B: M3 tapped holes 2 for customer chassis mounting (FG).
- C: Output pin : 2- $\phi 1.5$
- D: Input and Signal pin : 6- $\phi 1.0$
- E: Unless otherwise specified dimensional tolerance : ± 0.25 mm

(unit : mm)

MODEL NAME	PH75A280
TDK-Lambda	
C272-02-01B	