



**NOTES**

- A : M4 TAPPED HOLES  
12 POINTS FOR CUSTOMER CHASSIS MOUNTING.  
SCREWS MUST NOT BE PROTRUDE INTO POWER SUPPLY BY 7mm.
- B : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE,  
MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE  
AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE  
SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C :  $\perp$  IS PROTECTIVE BONDING TERMINAL.

TOLERANCE :  $\pm 1$ mm UNLESS OTHERWISE SPECIFIED.

**ACCESSORIES**

- \* SHORT PIECE (NET 2) FOR SHORTING PURPOSE  
(+S~+V, -S~-V) : MOUNTED AT TIME OF SHIPMENT.
- \* TERMINAL COVER 1 (NET 1)  
(MOUNTED AT TIME OF SHIPMENT)
- \* TERMINAL COVER 2 (NET 1)  
(MOUNTED AT TIME OF SHIPMENT)

(unit : mm)

MODEL NAME	RDS180A-24
<b>TDK-Lambda</b>	
A283-02-01A	