



| TOLERANCES/± | |
|----------------------|-------|
| L ≤ 16.0mm | 0.1 |
| 16.0 < L ≤ 63.0mm | 0.2 |
| 63.0 < L ≤ 250.0mm | 0.3 |
| 250.0 < L ≤ 1000.0mm | 0.5 |
| 1000 < L | 0.8 |
| ANGLE | ±0.5° |

- NOTE
1. MOUNTING HOLES FOR SLIDES P/N:CC3001-00-S160,GENERAL DEVICES OR EQUIVALENT.
USE #10-32x0.38INCH x3 SCREWS FOR EACH SLIDE.
ENSURE THAT THE SCREWS DO NOT PENETRATE MORE THAN 6.0mm INTO THE UNIT.
 2. AC INPUT RATING , SAFETY APPROVAL SYMBOLS AND EU REPRESENTATIVE ADDRESS LABEL
ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS.
 3. MODEL NAME , OUTPUT RATING AND COMPANY LOGO ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS.
 4. MOUNTING HOLES FOR 19" RACK, USE M6x16 SCREWS TO FIX THE UNIT TO THE RACK.

(unit : mm)

| | |
|-------------------|---------------------------|
| MODEL NAME | GEN+ HV 3PH 2.7;3.4;5.0KW |
| TDK-Lambda | |
| IA761-02-03D | |