



NOTE

1. MOUNTING SCREWS MUST NOT PROTRUDE INTO THE POWER SUPPLY MORE THAN 6mm.
2. EXTERNAL CONTROL CONNECTOR;
CONNECTOR: AMP, P/N 102617-5
RECEPTACLE: AMP, P/N 87631-9
RECEPTACLE CONTACTS: AMP, P/N 87523-5(STRIIP FORM)
P/N 87523-6(LOOSE PIECE)
WIRE AWG: 24 TO 20
HAND TOOL FOR WIRES CONNECTION: AMP, P/N 90202-2
3. RS232/RS485 COMMUNICATION
TIA/EIA-568A, SHIELDED, 8 CONTACTS CONNECTORS.
4. MODEL NAME AND OUTPUT RATING SHOWN HERE ACCORDING TO THE SPECIFICATION.
5. M6 OR 1/4" SCREW FOR LOAD WIRES CONNECTION.
6. INPUT VOLTAGE AND CURRENT RATING ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS
7. SAFETY AND EU REPRESENTATIVE ADDRESS LABEL.

(unit : mm)

| | |
|-------------------|--------------------|
| MODEL NAME | ZUP-200,400 SERIES |
| TDK-Lambda | |
| IA549-02-01B | |