

Certificate

Certificate no.

CU 72213953 01



License Holder:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Manufacturing Plant:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Test report no.: USA-DA 31781623 304

Client Reference: Boris Gorinshtein

Tested to: UL 61010-1:2012 R7.19
CAN/CSA-C22.2 NO. 61010-1-12 + GI1 + GI2 (R2017) + A1

Certified Product: Programmable Power Supply

License Fee - Units

Model Designation: see Appendix CDF (Constr. Data Form)

Rated Voltage:

1), 2), 3), 6), 7) Option 1: AC 190-240V; 3W + PE, 50/60Hz;
1), 2), 3), 6), 7) Option 2: AC 380-415V; 3W + PE, 50/60Hz;
1), 2), 3), 6), 7) Option 3: AC 380-480V; 3W + PE, 50/60Hz;
4), 5), 8), 9) Option 4: AC 100-240V; 50/60Hz;
6), 7) Option 5: AC 190-240V; 50/60Hz

contd.

Appendix: 1, 1-125

Licensed Test mark:



Date of Issue

(day/mo/yr)

02/11/2021

Certificate

Certificate no.

CU 72213953 02



License Holder:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Manufacturing Plant:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Test report no.: USA-DA 31781623 304

Client Reference: Boris Gorinshtein

Tested to:

UL 61010-1:2012 R7.19
CAN/CSA-C22.2 NO. 61010-1-12 + GI1 + GI2 (R2017) + A1

Certified Product: Programmable Power Supply

License Fee - Units

contd.

Rated Current:

Option 1: 1) 18.5A max., 2) 37A max., 3) 55.5A max.,
6) 10A max., 7) 12.5A max;
Option 2,3: 1) 9.2A max., 2) 18.4A max., 3) 27.6A max.,
6) 5.5A max., 7) 6.5A max;
Option 4: 4) 20A max., 5) 18.5A max., 8),9) 12.5A max;
Option 5: 6) 16.5A max., 7) 21A max.

Protection Class: I

Special Remarks: Replaces Certificate CU72201854.

Licensed Test mark:



Date of Issue

(day/mo/yr)
02/11/2021