



NOTES

- A. MODEL NAME , INPUT VOLTAGE RANGE , NOMINAL OUTPUT VOLTAGE & MAXIMUM OUTPUT CURRENT AND COUNTRY OF MANUFACTURE ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATION.
- B. SIDE SEAL DETAILS SHOWN HERE IS FOR REFERENCE ONLY. PLEASE SEE LATEST RELEASE FOR DETAILS.
- C. BARCODE, SERIAL NO. ARE SHOWN HERE.
- D. RECOMMENDED SCREW TORQUE M3.0: 4.4~5.9KGF.CM, M4.0: 11.5KGF.CM.
- E. RECOMMENDED WIRE: AWG10~20 (INPUT), AWG6~20 (OUTPUT).