

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Buffer Module

Name and address of the applicant

TDK-LAMBDA SINGAPORE PTE LTD
#06-01/08 1008 TOA PAYOH NORTH SINGAPORE 318996
SINGAPORE

Name and address of the manufacturer

TDK-LAMBDA SINGAPORE PTE LTD
#06-01/08 1008 TOA PAYOH NORTH SINGAPORE 318996
SINGAPORE

Name and address of the factory

*Note: When more than one factory, please report on page 2*TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA Additional Information on page 2

Ratings and principal characteristics

Input: 23.0 - 30.0 VDC, 20 A
Output: 22.4 VDC, 20 A
Buffer Time: 20A/0.25s (typ)

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

DBM20abcxxxxx
See Page 2

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E252373-A6016-CB-1 issued on 2020-07-23

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-24

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-100369-UL

Model Details:

DBM20abcxxxxx Where:

a can be "/" or blank

b can be E or blank

c can be CO or CO2 or blank

x can be blank or any alphanumeric character that is non safety related information

Factories:

TDK-LAMBDA MALAYSIA SDN BHD

LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD

NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028 CHINA

PANYU TRIO MICROTRONICS CO LTD

SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG 511453 CHINA

Additional Information:

Additionally evaluated to EN 62368-1:2014/ A11:2017.

National differences specified in the CB Test Report.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/mcbnames

Date: 2020-07-24

Signature:

Jan-Erik Storgaard