



- NOTE
1. MATING PLUG P/N:MC1.5/5-G-3.81 PHOENIX
 2. MOUNTING HOLES FOR SLIDES P/N:CC3001-00-S160,GENERAL DEVICES OR EQUIVALENT. USE #10-32x0.38INCH x3 SCREWS FOR EACH SLIDE. ENSURE THAT THE SCREWS DO NOT PENETRATE MORE THAN 6.0mm INTO THE UNIT.
 3. AC INPUT RATING AND SAFETY APPROVAL SYMBOLS ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS.
 4. STRAIN RELIEF DEVICE P/N: 1576.16.11 AGRO.
 5. MODEL NAME AND OUTPUT RATING ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS.
 6. MOUNTING HOLES FOR 19" RACK, USE M6x16 SCREWS TO FIX THE UNIT TO THE RACK.
 7. COMPANY LOGO IS SHOWN HERE.

ACCESSORIES

ITEM	PART NUMBER	QTY	PACKING	OUTER PACKING	NOTE
HEXAGONAL SCREW M10x25	DIN933 Cl. Cr.	2	PLASTIC BAG	PLASTIC BAG	FOR MODELS 60-100V ONLY INSULATOR IS ASSEMBLED TO THE BRACKET
HEXAGONAL NUT M10	DIN439B Cl. Cr.	2			
SPRING WASHER M10	DIN7980 Cl. Cr.	2			
FLAT WASHER M10	DIN125A Cl. Cr.	4			
SEMS SCREW M3x8		1	PLASTIC BAG	PLASTIC BAG	
FLAT HEAD SCREW M3x6		3	PLASTIC BAG		
PROTECTIVE BRACKET ASSEMBLY	IA626-32-19-00_	1	NONE		
PROTECTIVE BRACKET	IA626-32-10_	1	NONE	PLASTIC BAG	
PROT. BRACKET INSULATOR	IA626-33-03_	1	NONE		
LINKING CABEL	IA575-81-11_	1	PLASTIC BAG	PLASTIC BAG	
DB25 PLUG KIT	749809-9 AMP	1	PLASTIC BAG		
INPUT CONNECTOR PLUG	PC 6/3-STF-10,16 PHOENIX	1	NONE		
STRAIN RELIEF BRACKET	IA626-32-09-00_	1			
STRAIN RELIEF	1576.16.11 AGRO	1			
STRAIN RELIEF WASHER	8216 AGRO	1			
FLAT HEAD SCREW M3x8		2	PLASTIC BAG	PLASTIC BAG	
CASELEG	FF004-AR79 (SHINAWGAWA)	4	PLASTIC BAG		

(unit : mm)

MODEL NAME GEN3300W 8-100V 1PH

TDK-Lambda

IA626-02-03I