



CONNECTORS USED :

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	B3P5-VH(LF)(SN)	J.S.T	1
PIN HEADER (OUTPUT SIDE CN51)	B5P-VH(LF)(SN)	J.S.T	1

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
SOCKET HOUSING (CN1)	VHR-5N	J.S.T	1
SOCKET HOUSING (CN51)	VHR-5N	J.S.T	1

MATCHING PINS & TOOL (NOT INCLUDED WITH THE PRODUCT): NOTES :

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
TERMINAL PINS	SVH-21T-P1.1	J.S.T	8
	BVH-21T-P1.1		
HAND CRIMPING TOOL	YC-160R	J.S.T	-
PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
TERMINAL PINS	SVH-41T-P1.1	J.S.T	8
	BVH-41T-P1.1		
HAND CRIMPING TOOL	YC-930R	J.S.T	-
	YC-931R		

- A: $\varnothing 3.5$ HOLES FOR CUSTOMER'S CHASSIS MOUNTING.
- B: M3 TAPPED & EMBOSSED HOLES FOR CUSTOMER'S CHASSIS MOUNTING.
- C: $\varnothing 3.5$ HOLES FOR CUSTOMER'S CHASSIS MOUNTING.
- D: M3 TAPPED & STANDOFF HOLES FOR SAFETY GROUND CONNECTION.
- E: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, PEAK OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS)ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS. COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.
- F: \perp IS FOR SAFETY GROUND CONNECTION.

(unit : mm)

MODEL NAME	CUT35J/L
TDK-Lambda	

CA873-02-01/L-A