



ACCESSORIES

ITEM	PART NUMBER	QTY.	PACKING	OUTER PACKING	NOTE
HEXAGONAL SCREW M8x16	DIN933 Cl. Cr.	2	PLASTIC BAG	PLASTIC BAG	FOR 6V-60V MODELS ONLY.
HEXAGONAL NUT M8	DIN439B Cl.Cr.	2			
SPRING WASHER M8	DIN7980 Cl. Cr.	2			
FLAT WASHER M8	DIN125A Cl. Cr.	4			
SEMS SCREW M3x8		2	PLASTIC BAG	PLASTIC BAG	BUS BAR INSULATOR ASSEMBLED TO BUS BAR COVER
BUS BAR COVER	IA575-32-10_	1	NONE		
BUS BAR COVER INSULATOR	IA575-33-07_	1			
LINKING CABLE	IA575-81-11_	1	PLASTIC BAG		
DB25 PLUG KIT	749809-9 AMP	1	PLASTIC BAG		
STRAIN RELIEF BRACKET	IA575-32-07-00_	1	NONE	PLASTIC BAG	
STRAIN RELIEF	1576.16.11 AGRO	1			
STRAIN RELIEF WASHER	8216 AGRO	1			
FLAT HEAD SCREW M3x8		3	PLASTIC BAG		
PROTECTION BRACKET ASSEMBLY	IA575-32-15-00_	1		PLASTIC BAG	FOR 60V ONLY.

- NOTES
- MATING PLUG P/N: MC1.5/5-G-3.81 PHOENIX.
 - MOUNTING HOLES FOR SLIDES P/N: CC3001-00-S160, GENERAL DEVICES OR EQUIVALENT. USE 3x#10-32x0.38inch SCREWS FOR EACH SLIDE. ENSURE THAT THE SCREWS DO NOT PENETRATE MORE THAN 6.0mm INTO THE UNIT.
 - AC INPUT RATING AND SAFETY APPROVAL SYMBOLS ARE SHOWN HERE ACCORDING TO THE SPECIFICATION.
 - STRAIN RELIEF DEVICE P/N: 1576.16.11 AGRO.
 - MODEL NAME AND OUTPUT RATING ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS.
 - MOUNTING HOLES FOR 19" RACK, USE M6x16 SCREWS TO FIX THE UNIT TO THE RACK.
 - COMPANY LOGO IS SHOWN HERE.

(unit : mm)

MODEL NAME	GEN 1U 1500W-LV
TDK-Lambda	
IA575-02-01K	