

**HWS100A**

SPECIFICATIONS

A258-01-01A

| ITEMS |                                | MODEL      | HWS100A<br>-3  | HWS100A<br>-5 | HWS100A<br>-12 | HWS100A<br>-15 | HWS100A<br>-24 | HWS100A<br>-48 |     |
|-------|--------------------------------|------------|--|---------------|----------------|----------------|----------------|----------------|-----|
| 1     | Nominal Output Voltage         | V          | 3.3  | 5             | 12             | 15             | 24             | 48             |     |
| 2     | Maximum Output Current         | A          | 20   | 20            | 8.5            | 7              | 4.5            | 2.1            |     |
| 3     | Maximum Output Power           | W          | 66.0   | 100.0         | 102.0          | 105.0          | 108.0          | 100.8          |     |
| 4     | Efficiency (Typ.) (*1)         | 100VAC     | %  | 82            | 84             | 86             | 86             | 87             | 88  |
|       |                                | 200VAC     | %  | 84            | 86             | 88             | 88             | 89             | 90  |
| 5     | Input Voltage Range (*2)       | -          | 85 - 265VAC (47 - 63Hz) or 120 - 370VDC  |               |                |                |                |                |     |
| 6     | Input Current (Typ.) (*1)      | A          | 0.9/0.45   | 1.3/0.65      |                |                |                |                |     |
| 7     | Inrush Current (Typ.) (*1)(*3) | -          | 14A at 100VAC, 28A at 200VAC, Ta=25°C, Cold Start  |               |                |                |                |                |     |
| 8     | PFHC                           | -          | Designed to meet IEC61000-3-2  |               |                |                |                |                |     |
| 9     | Power Factor (Typ.) (*1)       | -          | 0.96/0.89  | 0.98/0.93     |                |                |                |                |     |
| 10    | Output Voltage Range           | V          | 2.97 - 3.96  | 4.0 - 6.0     | 9.6 - 14.4     | 12.0 - 18.0    | 19.2 - 28.8    | 38.4 - 52.8    |     |
| 11    | Maximum Ripple & Noise (*4)    | 0≤Ta≤70°C  | mV   | 120           | 120            | 150            | 150            | 150            | 200 |
|       |                                | -10≤Ta<0°C | mV   | 160           | 160            | 180            | 180            | 180            | 240 |
| 12    | Maximum Line Regulation (*5)   | mV         | 20   | 20            | 48             | 60             | 96             | 192            |     |
| 13    | Maximum Load Regulation (*6)   | mV         | 40   | 40            | 96             | 120            | 150            | 240            |     |
| 14    | Temperature Coefficient        | -          | Less than 0.02%/°C   |               |                |                |                |                |     |
| 15    | Over Current Protection (*7)   | A          | 21.0 ≤   | 21.0 ≤        | 8.92 ≤         | 7.35 ≤         | 4.72 ≤         | 2.20 ≤         |     |
| 16    | Over Voltage Protection (*8)   | V          | 4.13 - 4.95  | 6.25 - 7.25   | 15.0 - 17.4    | 18.8 - 21.8    | 30.0 - 34.8    | 55.2 - 64.8    |     |
| 17    | Hold-up Time (Typ.) (*1)       | -          | 20ms   |               |                |                |                |                |     |
| 18    | Leakage Current (*9)           | -          | Less than 0.5mA. 0.2mA (Typ) at 100VAC / 0.4mA (Typ) at 230VAC   |               |                |                |                |                |     |
| 19    | Remote Sensing                 | -          | Possible   |               |                |                |                |                |     |
| 20    | Parallel Operation             | -          | -  |               |                |                |                |                |     |
| 21    | Series Operation               | -          | Possible   |               |                |                |                |                |     |
| 22    | Operating Temperature (*10)    | -          | -10 to +70°C (-10 to +50°C:100%, +60°C:65%, +70°C:30%)   |               |                |                |                |                |     |
| 23    | Operating Humidity             | -          | 30 to 90%RH (No Condensing)  |               |                |                |                |                |     |
| 24    | Storage Temperature            | -          | -30 to +85°C   |               |                |                |                |                |     |
| 25    | Storage Humidity               | -          | 10 to 95%RH (No Condensing)  |               |                |                |                |                |     |
| 26    | Cooling                        | -          | Convection Cooling   |               |                |                |                |                |     |
| 27    | Withstand Voltage              | -          | Input - FG : 2kVAC (20mA), Input - Output : 3kVAC (20mA)<br>Output - FG : 500VAC (20mA) for 1min   |               |                |                |                |                |     |
| 28    | Isolation Resistance           | -          | More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC   |               |                |                |                |                |     |
| 29    | Vibration                      | -          | At no operating, 10 - 55Hz (Sweep for 1min)<br>19.6m/s <sup>2</sup> Constant, X,Y,Z 1hour each.  |               |                |                |                |                |     |
| 30    | Shock                          | -          | Less than 196.1m/s <sup>2</sup>  |               |                |                |                |                |     |
| 31    | Safety                         | -          | Approved by UL62368-1, CSA62368-1, EN62368-1, UL60950-1, CSA60950-1, EN60950-1 (Expire date of 60950-1 : 20/12/2020)<br>Designed to meet Den-an Appendix 8 at 100VAC only. |               |                |                |                |                |     |
| 32    | Line DIP                       | -          | Designed to meet SEMI-F47 (200VAC Line only)   |               |                |                |                |                |     |
| 33    | Conducted Emission (*11)       | -          | Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B  |               |                |                |                |                |     |
| 34    | Radiated Emission (*11)        | -          | Designed to meet EN55011/EN55032-B, FCC-B, VCCI-B  |               |                |                |                |                |     |
| 35    | Immunity (*11)                 | -          | Designed to meet IEC61000-6-2 IEC61000-4-2, -3, -4, -5, -6, -8, -11  |               |                |                |                |                |     |
| 36    | Weight (Typ)                   | -          | 420g   |               |                |                |                |                |     |
| 37    | Size (W x H x D)               | mm         | 28 x 82 x 160 ( Refer to Outline Drawing )   |               |                |                |                |                |     |

\*Read instruction manual carefully, before using the power supply unit.

=NOTES=

- \*1. At 100VAC/200VAC, Ta=25°C, nominal output voltage and maximum output power.
- \*2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100 - 240VAC(50 - 60Hz).
- \*3. Not applicable for the inrush current to Noise Filter for less than 0.2ms.
- \*4. Measure with JEITA RC-9131B probe, Bandwidth of scope :100MHz.
- \*5. 85 - 265VAC, constant load.
- \*6. No load-Full load, constant input voltage.
- \*7. Constant current limit and Hiccup with automatic recovery.  
Avoid to operate at over load or short circuit condition.
- \*8. OVP circuit will shut down output, manual reset (Re power on).
- \*9. Measured by the each measuring method of UL, CSA, EN and Den-an (at 60Hz), Ta=25°C.
- \*10. Output Derating  
- Derating at standard mounting. Refer to OUTPUT DERATING CURVE (A258-01-02 ).  
- Load (%) is percent of maximum output power or maximum output current, do not exceed its derating of maximum load.
- \*11. The power supply is considered a component which will be installed into a final equipment.  
The final equipment should be re-evaluated that it meets EMC directives.

**HWS100A**

OUTPUT DERATING

A258-01-02

| Ta (°C)   | LOAD (%)   | LOAD (%)   | LOAD (%)      |
|-----------|------------|------------|---------------|
|           | MOUNTING A | MOUNTING B | MOUNTING C, D |
| -10 - +40 | 100        | 100        | 100           |
| 50        | 100        | 80         | 80            |
| 60        | 65         | 60         | 60            |
| 70        | 30         | 30         | 20            |

