


FB Series

Thin-shaped molding process / Higher power La-Co type FB14H

Demagnetization curve



Magnetic characteristics

Material	FB14H		
Residual magnetic flux density B_r	(mT)	470 ± 10	$(4.7 \pm 0.1 \text{ kG})$
Coercive force H_{cB}	(kA/m)	355 ± 20	$(4.46 \pm 0.25 \text{ kOe})$
Intrinsic coercive force H_{cJ}	(kA/m)	430 ± 20	$(5.40 \pm 0.25 \text{ kOe})$
Maximum energy product $(BH)_{max}$	(kJ/m ³)	43.1 ± 1.6	$(5.4 \pm 0.2 \text{ MGOe})$

△ The details can be found by referring to the appended individual delivery specifications.
All specifications are subject to change without notice.