


FB Series

Thin-shaped molding process / Higher Power La-Co type FB13B

Demagnetization curve



Magnetic characteristics

Material	FB13B		
Residual magnetic flux density B_r	(mT)	475 ± 10	$(4.75 \pm 0.1 \text{ kG})$
Coercive force H_{cB}	(kA/m)	340 ± 20	$(4.27 \pm 0.25 \text{ kOe})$
Intrinsic coercive force H_{cJ}	(kA/m)	380 ± 20	$(4.77 \pm 0.25 \text{ kOe})$
Maximum energy product $(BH)_{max}$	(kJ/m³)	44.0 ± 1.6	$(5.5 \pm 0.2 \text{ MGOe})$

△ The details can be found by referring to the appended individual delivery specifications.
All specifications are subject to change without notice.