


## FB Series

Wet molding process / La-Co free type

### FB6B

Demagnetization curve



#### Magnetic characteristics

Material	FB6B		
Residual magnetic flux density $B_r$	(mT)	$420 \pm 10$	$(4.2 \pm 0.1 \text{ kG})$
Coercive force $H_{CB}$	(kA/m)	$302.4 \pm 12$	$(3.8 \pm 0.15 \text{ kOe})$
Intrinsic coercive force $H_{CJ}$	(kA/m)	$318.3 \pm 12$	$(4.0 \pm 0.15 \text{ kOe})$
Maximum energy product $(BH)_{max}$	(kJ/m <sup>3</sup> )	$33.4 \pm 1.6$	$(4.2 \pm 0.2 \text{ MGOe})$

△ The details can be found by referring to the appended individual delivery specifications.  
All specifications are subject to change without notice.