


CONNECTORS USED:

PART DESCRIPTION		PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SID	E CN1)	B3P5-VH	J.S.T.	1
PIN HEADER (OUTPUT S	IDE CN51)	B4P-VH	J.S.T.	1
PIN HEADER (OUTPUT S			J.S.T.	

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS, PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING (CN1)	VHR-5N	J.S.T.	1
SOCKET HOUSING (CN51)	VHR-4N	J.S.T.	1
TERMINAL PINS	SVH-21T-P1.1	ICT	7
	BVH-21T-P1.1	0.5.1.	/
HAND CRIMPING TOOL	YC-160R	J.S.T.	_
	BVH-21T-P1.1	J.S.T. J.S.T.	7



SCALE FOR NAME PLATE: 2/1

NOTES

- A: $4-\emptyset 3.5$ HOLES ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.
- B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, AND MAXIMUM OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C: COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
- D: \(\frac{1}{2} \) IS PROTECTIVE BONDING TERMINAL.
- E: TO KEEP THE DISTANCE MORE THAN 4mm BETWEEN PCB EDGE AND CUSTOMER'S CHASSIS.

