

SIGNAL CONNECTOR INFORMATION


CN1,CN2 PIN ASSIGNMENT  
S10B-PHDSS (JST)

1	+Vm
2	+S
3	-Vm
4	-S
5	NC
6	PC
7	PV
8	COM
9	CNT2
10	TOG

CN3 PIN ASSIGNMENT  
S8B-PHDSS (JST)

1	COM
2	COM
3	AUX
4	CNT1
5	G2
6	G2
7	ALM
8	G1

== NAME PLATE ==



SEE NOTE A

SEE NOTE B

== NOTES ==

- A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE AND NOMINAL OUTPUT CURRENT ARE ON NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B : COUNTRY OF MANUFACTURE IS SHOWN HERE.
- C : M4 TAPPED HOLES (12) FOR CUSTOMER CHASSIS MOUNTING. (SCREW PENETRATION DEPTH 6m/m MAX.)

== ACCESSORIES ==

\* SHORT PIECE -----1  
SHORTING +Vm - +S, -Vm - -S  
(ATTACHED ON CN1 AT SHIPMENT)

== SIGNAL CONNECTOR USED ==

PART DESCRIPTION	PART NAME	MANUFACT
PIN HEADER (CN1 & CN2)	S10B-PHDSS	JST
PIN HEADER (CN3)	S8B-PHDSS	JST

== MATCHING HOUSINGS , PINS & TOOL ==

PART DESCRIPTION	PART NAME	MANUFACT
SOCKET HOUSING (CN1 & CN2)	PHDR-10VS	JST
SOCKET HOUSING (CN3)	PHDR-8VS	JST
TERMINAL PINS	SPHD-002T-P0.5(AWG28~24) SPHD-001T-P0.5(AWG26~22)	JST
HAND CRIMPING TOOL	YRS-620(SPHD-002T-P0.5) YC-610R(SPHD-001T-P0.5)	JST

(unit : mm)

MODEL NAME	HWS1000L/BAT
<b>TDK-Lambda</b>	
CA772-02-01/BAT-D	