


Multilayer Chip Directional Couplers For W-CDMA


Conformity to RoHS Directive

HHM Series HHM2910E9

SHAPES AND DIMENSIONS



RECOMMENDED PC BOARD PATTERNS



ELECTRICAL CHARACTERISTICS

Frequency range		1920 to 1980MHz	2110 to 2170MHz
Coupling factor		20.1±1.0dB	19.3±1.0dB
Insertion loss		0.22dB max.*1	0.22dB max.*1
		0.25dB max.*2	0.25dB max.*2
Isolation		34dB min.	34dB min.
VSWR		1.4max.	1.4max.
Temperature range	Operating	-40 to +85°C	-40 to +85°C
	Storage	-40 to +85°C	-40 to +85°C

*1 25°C


*2 Operating temperature

• Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.


• All specifications are subject to change without notice.

FREQUENCY CHARACTERISTICS


COUPLING



ISOLATION & DIRECTIVITY



INSERTION LOSS



VSWR

