



CONNECTOR USED :

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	5414-30B OR 5273-06A(1.4.6)	MOLEX	1
PIN HEADER (OUTPUT SIDE CN2)	5273-10A	MOLEX	1
PIN HEADER (OUTPUT SIDE CN3)	B2B-XH-A	JST	1

* CURRENT OF THE CN2 CONNECTOR PIN MUST BE LESS THAN 5A (7A AT PEAK LOAD)

RECOMMENDED HOUSING & TERMINAL PIN :

* NOT INCLUDED WITH THE PRODUCT.

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
SOCKET HOUSING (CN1)*1	5195-06	MOLEX	1
SOCKET HOUSING (CN2)*1	5195-10	MOLEX	1
SOCKET HOUSING (CN3)*2	XHP-2	JST	1
TERMINAL PINS (CN1, CN2)	5194PBT	MOLEX	13
TERMINAL PINS (CN3)*2	BXH-001T-P0.6 OR SXH-001T-P0.6	JST	2

HAND CRIMPING TOOL : 11-26-0058 CN1,CN2 MANUFACTURER : MOLEX
 HAND CRIMPING TOOL : YC-110R OR YRS-110 CN3 MANUFACTURER : JST

*1 FOLLOWING HOUSING ARE RECOMMENDED AS EQUIVALENT PARTS

MAIN PARTS	SUB PARTS 1	SUB PARTS 2
5195-06	09-50-3061 (MOLEX) (2139-06)	09-91-0600 (MOLEX) (3069-06)
5195-10	09-50-3101 (MOLEX) (2139-10)	09-91-1000 (MOLEX) (3069-10)

*2 APPLICABLE ONLY WHEN USING REMOTE ON/OFF

== NAME PLATE ==

ZWD225PAF-0524 TDK-Lambda

INPUT : 100-240VAC~3.0A
50/60Hz

OUTPUT: 5V \equiv 5.0A CE

24V \equiv 9.0A TUV

RATED POWER : 225W

24V : 14/18A PEAK @ 100/200VAC

MADE IN CHINA cRU

TÜV
Rheinland
Product Safety

BAUART
GEPRÜFT

TYPE
APPROVED

SEE NOTE C

== NOTE ==

- A. THE 5- ϕ 3.5 HOLES ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLE. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.
- B. MODEL NAME, INPUT VOLTAGE RANGE, AVERAGE OUTPUT POWER, NOMINAL OUTPUT VOLTAGE, AVERAGE OUTPUT CURRENT AND PEAK OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C. COUNTRY OF MANUFACTURER WILL BE SHOWN HERE.
- D. TO KEEP A DISTANCE MORE THAN 4.5mm FROM PC-BOARD EDGE, LEAD CUT AND COMPONENT HEIGHT TO CUSTOMER'S CHASSIS.
- E. FG IS FOR SAFETY GROUND CONNECTION.
- F. CN3 IS NORMALLY SHORTED BY JM-2W-96(JST). IF USING REMOTE ON/OFF, REMOVE JM-2W-96 AND REFER TO THE TABLE FOR RECOMMENDED HOUSING AND TERMINAL PIN.

(unit : mm)

MODEL NAME	ZWD225PAF
TDK-Lambda	

PA574-02-01H