


NAME PLATE



SEE NOTE A

= NOTES =

- A: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT AND COUNTRY OF MANUFACTURE ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B: 4- $\phi$ 3.5 HOLES FOR CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.
- C: KEEP THE DISTANCE MORE THAN 4mm BETWEEN POWER SUPPLY EDGE AND CUSTOMER'S CHASSIS.
- D: FG IS FOR SAFETY GROUND CONNECTION.
- E: REMOTE ON/OFF CONTROL CONNECTOR (CN2,53) : B2B-XH-AM (J.S.T.)  
MATCHING HOUSING : XHP-2 (J.S.T.)  
MATCHING TERMINAL : BXH-001T-P0.6 (J.S.T.) OR SXH-001T-P0.6 (J.S.T.)  
\*CN2 IS NORMALLY SHORTED BY JM-2W-96(J.S.T.).  
\*HAND CRIMPING TOOL: YC-110R or YSR-110 (J.S.T)
- F: CONNECTOR TO CHANGE V2,V3 OUTPUT VOLTAGE (CN71) : B4B-XH-AM (J.S.T.)  
J61 SHORT : V2 OUTPUT VOLTAGE IS +12V.(\*)  
J61 OPEN : V2 OUTPUT VOLTAGE IS +15V.  
J71 SHORT : V3 OUTPUT VOLTAGE IS -12V.(\*)  
J71 OPEN : V3 OUTPUT VOLTAGE IS -15V.  
\*J61 AND J71 ARE NORMALLY SHORTED BY JM-2W-96(J.S.T.).

CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B3P-5-VH	J.S.T.	1
PIN HEADER (OUTPUT SIDE CN51)	B8P-VH	J.S.T.	1
PIN HEADER (OUTPUT SIDE CN61)	B3P-VH	J.S.T.	1
PIN HEADER (OUTPUT SIDE CN81)	B6P-VH	J.S.T.	1

\*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A

MATCHING HOUSINGS & PINS (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING (CN1)	VHR-5N	J.S.T.	1
SOCKET HOUSING (CN51)	VHR-8N	J.S.T.	1
SOCKET HOUSING (CN61)	VHR-3N	J.S.T.	1
SOCKET HOUSING (CN81)	VHR-6N	J.S.T.	1
TERMINAL PINS (CN1,51,61,81)	SVH-21T-P1.1	J.S.T.	20

\*HAND CRIMPING TOOL: YC-160R

MANUFACT: J.S.T

(unit : mm)

MODEL NAME	ZWQ130
<b>TDK-Lambda</b>	

A191-02-01B