

# FG22X7R1H335KNT06




## Application

Commercial Grade

## Series

FG22



## Dimensions

- L 7.5mm Max.
- W 8.5mm Max.
- T 4.5mm Max.
- F 5mm +0.8,-0.2mm
- d 0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 125°C +/-15%

## Rated Voltage

50Vdc

## Capacitance

3.3uF

## Capacitance Tolerance

+/-10%

## Dissipation Factor





3% Max.

## Insulation Resistance

151Mohm Min.

## AEC-Q200

No



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

September 8, 2017