

DRB240-24-1

SPECIFICATIONS

PA635-01-01

ITEMS	MODEL	DRB240-24-1
1	Nominal Output Voltage	V 24
2	Maximum Output Current	A 10
3	Peak Output Current (*12)	A 12
4	Maximum Output Power	W 240
5	Peak Output Power (*12)	W 288
6	Efficiency (Typ) (115/230VAC) (*1)	% 91/93
7	Active Average Efficiency Related to ErP (Typ) (230VAC) (*1)	% 87
8	Input Voltage Range (*2)	V 85 ~ 264VAC (47-63Hz) (Withstand 300VAC Surge for 5 seconds)
9	Input Current (Typ) (115/230VAC) (*1)	A 2.4 / 1.4
10	Inrush Current (Typ) (230VAC) (*3)	A 55A
11	PFHC	- Designed To Meet IEC61000-3-2
12	Power Factor (Typ) (115/230VAC) (*1)	- 0.98 / 0.92
13	Output Voltage Range	V 24~28
14	Ripple & Noise (*1,4)	mV 240
15	Line Regulation (*5,6)	mV 24
16	Load Regulation (*5,7)	mV 240
17	Temperature Coefficient	- Less than 0.02% / °C
18	Over Current Protection (*8)	- Hiccup
19	Over Voltage Protection (*9)	V 30~35
20	Hold-up Time (Typ) (*1)	ms 20
21	Leakage Current (*10)	- < 1mA at 230VAC
22	Monitoring Signal	- DC OK (Photocoupler Rated : 50V, 5mA), DC OK LED
23	Series Operation	- Possible
24	Parallel Operation	- No
25	Operating Temperature (*11)	- -25~+55°C : 100%, +70°C : 50%
26	Operating Humidity	- 5~95%RH (No dewdrop)
27	Storage Temperature	- -40°C ~ +85°C
28	Storage Humidity	- 5~95%RH (No dewdrop)
29	Cooling	- Convection Cooling
30	Withstand Voltage	- Input - Output : 4243VDC (20mA), Input - FG : 2500VDC (20mA) Output - FG : 707VDC (100mA) For 1min.
31	Isolation Resistance	- Input - FG, Input - Output and Output - FG More than 100MΩ (500VDC) at 25°C and 70%RH
32	Vibration	- At no operating, 10 - 55Hz (sweep for 1min) 19.6m/s ² (2G) Constant, X, Y, Z 1hour each.
33	Shock/(In Package)	- Less Than 196 m/s ² (20G)
34	Operating Altitude	- 3000m
35	Safety	- Approved by UL60950-1, CSA22.2 No. 60950-1-07 IEC/EN60950-1, UL 62368-1, CSA C22.2 No. 62368-1-14, IEC/EN 62368-1, CSA C22.2 No.107.1-16, UL508
36	EMI	- Designed to meet EN55011-B, EN55032-B, EN61204-3 CLASS A
37	CE	- LVD, RoHS 2, EMC
38	Immunity	- Designed to meet EN61000-4-2 (Level 4), -3 (Level 3), -4 (Level 4), -5 (Level 4), -6 (Level 3), -8 (Level 4), -11
39	Weight(Typ.)	g 750
40	Size (W x D x H)	mm 41 x 125 x 124 (Refer to Outline drawing)

* Read instruction manual carefully , before using the power supply unit.

=NOTES=


- *1. At Maximum Output Power, nominal input voltage, Ta = 25°C.
- *2. For cases where conformance to various safety specs (UL, CSA, EN) are required, to be described as 100-240VAC, 50/60Hz on name plate.
- *3. Not applicable for the in-rush current to Noise Filter for less than 0.2ms.
- *4. Ripple & noise are measured at 20MHz by using a 300mm twisted pair of load wires terminated with a 0.1uF Film Capacitor and a 47uF Electrolytic Capacitor.
- *5. Measure line & load regulation at output terminal.
- *6. 85 - 264VAC, constant load.
- *7. No load - Full load, constant input voltage.
- *8. Over rated current (>101%) of peak power.
- *9. Output latched shut down at no load and hiccup at any load. Manual reset by AC cycle.
- *10. Measured by each measuring method of UL and EN (at 60Hz), Ta = 25°C.
- *11. Refer to Output Derating Curve (PA635-01-02_) for details of output derating versus ambient temperature.
- *12. Operating period at peak output current is D≤ 35%, <10sec and 10Arms max.
- *13. All parameters not specifically mentioned are measured at 230VAC input, rated load and Ta = 25°C.

DRB240-24-1

PA635-01-02

DERATING CURVE

***COOLING : CONVECTION COOLING**

Ta (°C)	LOAD (%)	STANDARD MOUNTING
-25 ~ +55	100	
70	50	

